

# Special Track Work Complete Welder Pair, Power



## FEATURES

Designed for bonding structures in power bond applications

To be used with factory-formed terminals

Includes mold cleaner and flint ignitor

## SPECIFICATIONS

Table 1/1

| Catalog Number | Material        | Connects To        | Bond Terminal Style | Conductor Size    | Conductor Outer Diameter, Nominal | Welder Style |
|----------------|-----------------|--------------------|---------------------|-------------------|-----------------------------------|--------------|
| PBJT52W        | Steel, Graphite | Flat Steel Surface | J                   | 250 kcmil Ropelay | 19.05mm                           | T5           |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**⚠ WARNING:** This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**