

DMH Metallic Spacer



CERTIFICATIONS



FEATURES

To make higher plates, screens or profiles

Male-female allowing stable mounting

SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel

Table 1/2

Catalog Number	Article Number	Thread Size (TS)	Thread Length (TL)	Thread Depth (TD)	Length (L)	Width (W)
DMH-M4X10	561560	M4	8mm	10mm	10mm	7 mm
DMH-M4X15	561570	M4	8mm	10mm	15mm	7 mm
DMH-M4X20	561580	M4	8mm	10mm	20mm	7 mm

CatalogNumber	Article Number	Thread Size (TS)	Thread Length (TL)	Thread Depth (TD)	Length (L)	Width (W)
DMH-M4X25	561590	M4	8mm	10mm	25mm	7 mm
DMH-M4X30	561600	M4	8mm	10mm	30mm	7 mm
DMH-M4X35	561610	M4	8mm	10mm	35mm	7 mm
DMH-M4X40	561620	M4	8mm	10mm	40mm	7 mm
DMH-M5X15	561660	M5	10mm	10mm	15mm	8 mm
DMH-M5X20	561670	M5	10mm	10mm	20mm	8 mm
DMH-M5X25	561680	M5	10mm	10mm	25mm	8 mm
DMH-M5X30	561690	M5	10mm	10mm	30mm	8 mm
DMH-M5X35	561700	M5	10mm	10mm	35mm	8 mm
DMH-M6X15	561760	M6	10mm	10mm	15mm	10 mm
DMH-M6X20	561770	M6	10mm	10mm	20mm	10 mm
DMH-M4X50	561630	M4	8mm	10mm	50mm	7 mm
DMH-M4X60	561640	M4	8mm	10mm	60mm	7 mm
DMH-M5X40	561710	M5	10mm	10mm	40mm	8 mm
DMH-M5X50	561720	M5	10mm	10mm	50mm	8 mm
DMH-M6X30	561780	M6	10mm	10mm	30mm	10 mm
DMH-M5X60	561730	M5	10mm	10mm	60mm	8 mm
DMH-M5X70	561740	M5	10mm	10mm	70mm	8 mm

CatalogNumber	Article Number	Thread Size (TS)	Thread Length (TL)	Thread Depth (TD)	Length (L)	Width (W)
DMH-M5X80	561750	M5	10mm	10mm	80mm	8 mm
DMH-M6X40	561790	M6	10mm	10mm	40mm	10 mm
DMH-M6X50	561800	M6	10mm	10mm	50mm	10 mm
DMH-M6X60	561810	M6	10mm	10mm	60mm	10 mm
DMH-M6X70	561820	M6	10mm	10mm	70mm	10 mm
DMH-M6X80	561830	M6	10mm	10mm	80mm	10 mm
DMH-M6X100	561850	M6	10mm	10mm	100mm	10 mm
DMH-M6X90	561840	M6	10mm	10mm	90mm	10 mm

Table 2/2		
Catalog Number	Article Number	Unit Weight
DMH-M4X10	561560	0 kg
DMH-M4X15	561570	0.01 kg
DMH-M4X20	561580	0.01 kg
DMH-M4X25	561590	0.01 kg
DMH-M4X30	561600	0.01 kg
DMH-M4X35	561610	0.01 kg
DMH-M4X40	561620	0.01 kg
DMH-M5X15	561660	0.01 kg
DMH-M5X20	561670	0.01 kg

Catalog Number	Article Number	Unit Weight
DMH-M5X25	561680	0.01 kg
DMH-M5X30	561690	0.01 kg
DMH-M5X35	561700	0.01 kg
DMH-M6X15	561760	0.01 kg
DMH-M6X20	561770	0.01 kg
DMH-M4X50	561630	0.02 kg
DMH-M4X60	561640	0.02 kg
DMH-M5X40	561710	0.02 kg
DMH-M5X50	561720	0.02 kg
DMH-M6X30	561780	0.02 kg
DMH-M5X60	561730	0.03 kg
DMH-M5X70	561740	0.03 kg
DMH-M5X80	561750	0.03 kg
DMH-M6X40	561790	0.03 kg
DMH-M6X50	561800	0.03 kg
DMH-M6X60	561810	0.04 kg
DMH-M6X70	561820	0.04 kg
DMH-M6X80	561830	0.05 kg

Catalog Number	Article Number	Unit Weight
DMH-M6X100	561850	0.06 kg
DMH-M6X90	561840	0.06 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE