

Hazardous Location Window Kits

Hazardous Location Window Kits are designed to be used on Increased Safety (Ex e) enclosures in ATEX or IECEx Zone 1 or 2 hazardous areas. These window kits ensure a dust-, oil-, and water-tight seal. Designed for use as viewing windows, these window kits are ideal for visibility of internal enclosure components. The windows are easily installed by making a cutout in the enclosure and attaching the window and frame with included mounting hardware.

INDUSTRY STANDARDS

UL 508A Component Recognized; Type 4, 4X, 12, 3R; File No. E61997

IECEx and ATEX Approvals

Suitable for use on increased safety enclosures for ZONE 1 or ZONE 2 assemblies

ATEX Directive 94/9/EC

ATEX

Sira 13ATEX3315U

Ex e IIC Gb

Ex tb IIIC Db IP 66

IECEx

IECEx SIR 13.0123U

Ex e IIC Gb

Ex tb IIIC Db IP 66

cUR Component Recognized per CSA C22.2 No. 94; Type 4, 4X, 12,

3R; File No. E61997

NEMA/EEMAC 4, 4X, 12, 13

IEC 60529, IP66



FEATURES

Secure sealing with silicon gasket to protect against water and dust ingress in high-temperature applications

Maintain visual on components through .25-in. (6-mm) tempered safety glass

Easy installation in enclosure cutouts with window frame hardware

SPECIFICATIONS

Finish: Brushed
Material: Stainless Steel 316L

Table 1/1				
Catalog Number	Article Number	Thickness	Cutout Size	Quick Ship
EXWK138SS6	27024	1.98mm	373 x 246mm	No
EXWK53SS6	27021	1.98mm	170 x 119mm	No
EXWK95SS6	27022	1.98mm	272 x 183mm	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE