We connect and protect

Front Panel, Front Shielded, Side Hinged

Power Utilities

Front panel with textile EMC gasket, side hinged assembly.

CERTIFICATIONS

RoHS COMPLIANT

FEATURES

- Front panel with textile EMC gasket
- Enables mounting onto the horizontal rails
- Suitable for subracks and cases
- Hinges can be fitted on left or right

SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Package Quantity	Mounting	Gasket Type	Front Finish	Rear Finish
20848-617	6 U	1	Hinged, Side	Textile	Anodized	Conductive
20848-611	3 U	1	Hinged, Side	Textile	Anodized	Conductive

Table 2/3

Catalog Number	Treated Edges	EMC Shielding	Height	Material	Product Type	Rack Width
20848-617	No	No (Retrofittable)	261.8 mm	Aluminum	Front Panel	84 HP
20848-611	No	No (Retrofittable)	128.4 mm	Aluminum	Front Panel	84 HP

Table 3/3

Catalog Number	Type	Width
20848-617	Front Panel without Handle	426.4 mm
20848-611	Front Panel without Handle	426.4 mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.