

Varistar CP Steel Door, Perforated With 3-Point Electronic Locking

Power Utilities

Varistar CP perforated steel door 3-point locking for IP 20 applications.

FEATURES

Perforated steel door with 3-point locking for IP 20 protection class

Lever handle with built-in push button

Opening angle 180°

SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Height	Width	Type	Color	Color Code
21630-814	42 U	2000 mm	600 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-815	47 U	2200 mm	600 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-816	52 U	2450 mm	600 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-817	42 U	2000 mm	800 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-818	47 U	2200 mm	800 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-819	52 U	2450 mm	800 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-895	42 U	2000 mm	600 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-896	47 U	2200 mm	600 mm	Steel Door, Perforated	Black Grey	RAL 7021

CatalogNumber	Rack Height	Height	Width	Type	Color	Color Code
21630-897	52 U	2450 mm	600 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-898	42 U	2000 mm	800 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-899	42 U	2000 mm	800 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-900	52 U	2450 mm	800 mm	Steel Door, Perforated	Black Grey	RAL 7021

Table 2/3						
Catalog Number	Complies With	Finish	Locking Type	Material	Product Type	Protection Rating
21630-814	IEC 61587-1	Powder Coated	3-Point Locking, Electronic	Steel	Cabinet Door	IP20
21630-815	IEC 61587-1	Powder Coated	3-Point Locking, Electronic	Steel	Cabinet Door	IP20
21630-816	IEC 61587-1	Powder Coated	3-Point Locking, Electronic	Steel	Cabinet Door	IP20
21630-817	IEC 61587-1	Powder Coated	3-Point Locking, Electronic	Steel	Cabinet Door	IP20
21630-818	IEC 61587-1	Powder Coated	3-Point Locking, Electronic	Steel	Cabinet Door	IP20
21630-819	IEC 61587-1	Powder Coated	3-Point Locking, Electronic	Steel	Cabinet Door	IP20
21630-895	IEC 61587-1	Powder Coated	3-Point Locking, Electronic	Steel	Cabinet Door	IP20
21630-896	IEC 61587-1	Powder Coated	3-Point Locking, Electronic	Steel	Cabinet Door	IP20
21630-897	IEC 61587-1	Powder Coated	3-Point Locking, Electronic	Steel	Cabinet Door	IP20
21630-898	IEC 61587-1	Powder Coated	3-Point Locking, Electronic	Steel	Cabinet Door	IP20
21630-899	IEC 61587-1	Powder Coated	3-Point Locking, Electronic	Steel	Cabinet Door	IP20
21630-900	IEC 61587-1	Powder Coated	3-Point Locking, Electronic	Steel	Cabinet Door	IP20

Table 3/3

Catalog Number	Works With
21630-814	Varistar CP
21630-815	Varistar CP
21630-816	Varistar CP
21630-817	Varistar CP
21630-818	Varistar CP
21630-819	Varistar CP
21630-895	Varistar CP
21630-896	Varistar CP
21630-897	Varistar CP
21630-898	Varistar CP
21630-899	Varistar CP
21630-900	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle separately.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE