

AMC-F5 Mechanical Thermostat



nVent RAYCHEM AMC-F5 is a thermostat for pipe freeze protection heat tracing applications in non-hazardous locations. It has a fixed set point of 40 °F/5 °C, used in either ambient or surface sensing modes, it can control a single heat tracing circuit or switch multiple circuits through a contactor.

FEATURES

Simple to install and operate, single cable entry through 3/4" (19 mm) through hole

Energy saving, ambient or line sensing control thermostat

Electrical rating and switch: 22 A at 125/250/480 VAC, SPST switch

Enclosure: TYPE 4X, UV-resistant, thermoplastic

Reliable during long life: 2 year product warranty available, maintenance free

SPECIFICATIONS

Table 1/2

Catalog Number	Item Name	Thermostat Type	Material	NEMA Rating	Supply Voltage	Current Rating
031661-000	AMC-F5	Electronic	Thermoplastic	4X	120 – 480 V	22 A

Table 2/2

Catalog Number	Item Name	Fixed Temperature Set Point	Height	Width	Depth
031661-000	AMC-F5	5 °C	132 mm	81 mm	64 mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT