nVent SCHROFF

We connect and protect

# VMEbus System, 7 U, 12 Slot, Open Frame PSU

## CATALOG NUMBER

**20836-715**



VME system for 12 VME boards 6 U, 160 mm. The power for the system is supplied by an open frame power supply. A fan control module monitors the fans, the temperature and voltage.

## CERTIFICATIONS

RoHS COMPLIANT

VITA Open Standards, Open Markets

## FEATURES

- System in accordance with IEC 60297-3-101, -102, -103; IEEE 1101.1, 1101.10/11; Backplane conforms to VITA 1.1-1994
- PSU, open frame, 444 W (400 W at < 180 VAC)
- Backplane VME 12 slot, 6 U, J1/J2 monolithic in accordance with VITA 1-1994
- Heat dissipation by 1 fans (fan tray), cooling bottom to top; temperature-controlled with fan control module (FCM)
- Display module for DC operating voltages, fan and temperature alarm

## PRODUCT ATTRIBUTES

- Product Type: System
- Number of Slots: 12
- Type: 19" Rack Mount
- Backplane Type: 6 U VME64
- Data Transfer: VME64; VME2eSST

Power per Slot: 30W

Input Voltage AC: 100 – 240V

Airflow Direction: Bottom to Top

Rack Height: 7U

Power Supply Type: Open Frame

Power Supply Included: Yes

Rear I/O: No

Complies With: ANSI/VITA 1.1-1994

Depth: 355mm

Height: 310.35mm

Width: 449mm

Power: 450W

Package Quantity: 1

## ADDITIONAL PRODUCT DETAILS

Modified systems available on request.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.


**North America**
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

**Europe**
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

**Asia**
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

**Middle East & India**
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff


Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE


©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.