

40 Wedge-Lok

CATALOG NUMBER

40-15-LF-LN-M



Economical Card Lok designed for PCB retention and thermal transfer within cold wall applications.

⚠WARNING: This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to www.P65Warnings.ca.gov.

FEATURES

3 segment, non-shafted design

Screw actuated

Flexible mounting options

Length 50.8 mm (2.0") to 304.8 mm (12.0"), 12.7 mm (0.5") increments

Weight 1.07 g/cm (0.096 oz./")

Available with gold chem film, clear chem film, black anodized, hard black anodized, or electroless nickel plating

DSCC 84103 / DSCC CID 59590

Profile 5.72 mm (0.225 in) x 6.60 mm (0.260")

Max expansion 8.38 mm (0.330")

For cold wall applications

Average clamp force (5", black anodized) = 272 lbs

PRODUCT ATTRIBUTES

Product Type: PCB Retainer

Material: Aluminum

Clamp Force: 91 – 136kgf

Gap Width: PCB + (7.0 - 7.9 mm)

ADDITIONAL PRODUCT DETAILS

From time to time, nVent may modify its product specifications to be in conformity with applicable industry, military or other relevant standards. Unless otherwise mutually agreed in writing, cancelled or superseded military specifications may be certified to the latest or superseding specifications. Products manufactured in conformity with such specifications will be

deemed fully compliant whether or not you have been notified of such modifications, even if different from the original specification or those referenced by the customer.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ **WARNING:** This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to www.P65Warnings.ca.gov.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE