

# PSU 19" AC/DC Linear Regulator, Triple

Linear regulator for applications requiring very low output noise level.



## CERTIFICATIONS



## FEATURES

3 output voltages, galvanically separated

High control accuracy, low residual ripple and very low interference

Mains/line voltage 230 VAC (can be switched to 115 VAC with mains/line voltage conversion kit)

Suited for medical applications (8 mm safety clearances)

## SPECIFICATIONS

Table 1/3

Catalog Number	Type	Input Voltage AC	Power	Number of Output Voltages	Voltage 1	Current 1
13105-051	19" Linear Regulator	230V	8W	3	5V	0.5A
13105-052	19" Linear Regulator	230V	20W	3	5V	1.5A
13105-053	19" Linear Regulator	230V	39W	3	5V	3A

Table 2/3

Catalog Number	Voltage 2	Current 2	Voltage 3	Current 3	Rack Height	Rack Width
13105-051	12V	0.2A	12V	0.2A	3U	6HP
13105-052	12V	0.5A	12V	0.5A	3U	10HP
13105-053	12V	1A	12V	1A	3U	14HP

Table 3/3

Catalog Number	Depth	Package Quantity	Certifications	Quick Ship
13105-051	171.93mm	1	CE, EN 62368-1, RoHS	No
13105-052	171.93mm	1	CE, RoHS	No
13105-053	171.93mm	1	CE, RoHS	No

## ADDITIONAL PRODUCT DETAILS

Please order Front Panel separately.

Output Data at Ta= 0 ... 50 °C.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**