


# 510 nVent CADDY EZ Riser



The 510 nVent CADDY EZ Riser is a quick-closing pipe clamp, ideal for supporting vertical steel pipe where space is available. Ready-to-use out of the box, this solution has slotted holes to simplify assembly and eliminate loose hardware. Due to the serrated washer-head design, installers can easily assemble the EZ Riser with just a single tool.

## CERTIFICATIONS



## FEATURES

Only one tool needed to tighten due to serrated wash-heads

Conforms with Federal Specification WW-H-171 (Type 8), Manufacturers Standardization Society (MSS) SP-58 (Type 8)

## SPECIFICATIONS

**Finish:** Electrogalvanized

**Material:** Steel

Table 1/2

| Catalog Number | Article Number | NB/DN | Outer Diameter (OD) | Hole Size (HS) | A      | B     |
|----------------|----------------|-------|---------------------|----------------|--------|-------|
| 5101200EG      | 179338         | 300   | 324 mm              | 17 mm          | 569 mm | 51 mm |
| 5100800EG      | 179336         | 200   | 219 mm              | 17 mm          | 464 mm | 51 mm |
| 5101000EG      | 179337         | 250   | 273 mm              | 17 mm          | 524 mm | 51 mm |

Table 2/2

| Catalog Number | Article Number | Static Load | Certifications |
|----------------|----------------|-------------|----------------|
| 5101200EG      | 179338         | 12000N      |                |
| 5100800EG      | 179336         | 11100N      | UL, cUL        |
| 5101000EG      | 179337         | 11100N      |                |

## ADDITIONAL PRODUCT DETAILS

Clamp is fitted for steel pipe and should be installed below a coupling or shear lug, with bolts torqued to recommended value.

Slotted holes and bolts for pipe sizes up to 12" only.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**

