

Strike Point, Metric Thread



FEATURES

Mounts to metric threaded stud

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Diameter (Ø)	Height (H)	Thread Size (TS)	Unit Weight
ARC2205CNC	101900	Copper	16 mm	0.5 m	M10	0.55 kg
ARC2205SS	102000	Stainless Steel 304 (EN 1.4301)	16 mm	0.5 m	M10	0.5 kg
ARC2210CNC	101910	Copper	16 mm	1 m	M10	0.8 kg
ARC2210SS	102010	Stainless Steel 304 (EN 1.4301)	16 mm	1 m	M10	0.75 kg

Table 2/2

Catalog Number	Article Number	Complies With
ARC2205CNC	101900	IEC® EN 62561-2
ARC2205SS	102000	

Catalog Number	Article Number	Complies With
ARC2210CNC	101910	IEC® EN 62561-2
ARC2210SS	102010	IEC® EN 62561-2

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE