

# P13 Position Coupler, Male and Nut Only, Worldwide Design



Used in segmental pour and closure pour applications. Male and female components are sold separately.

## FEATURES

Designed to splice two curved, bent or straight bars, when neither bar can be rotated and where the ongoing bar is NOT free to move in its axial direction

Adjustability in the female end of the coupler allows the coupler to extend out to meet the taper-threaded reinforcing bar

## SPECIFICATIONS

<b>Finish:</b>	Plain
<b>Coupler Adjustment:</b>	Standard
<b>Material:</b>	Steel

Table 1/2

Catalog Number	Rebar Size, Metric	Rebar Size, US	Rebar Size, Canada	Diameter (Ø)	Length (L)	A
EL10P13LMN	10 mm	#3		20 mm	95mm	50 mm
EL12P13LMN	12 mm	#4	10M	20 mm	99mm	49 mm
EL14P13LMN	14 mm			20 mm	106mm	52 mm
EL16P13LMN	16 mm	#5	15M	25 mm	113mm	55 mm

CatalogNumber	Rebar Size, Metric	Rebar Size, US	Rebar Size, Canada	Diameter (Ø)	Length (L)	A
EL18P13LMN	18 mm			25 mm	125mm	61 mm
EL20P13LMN	20 mm	#6	20M	30 mm	155mm	73 mm
EL22P13LMN	22 mm	#7		35 mm	164mm	78 mm
EL25P13LMN	25 mm	#8	25M	35 mm	172mm	81 mm
EL28P13LMN	28 mm	#9	30M	40 mm	178mm	82 mm
EL32P13LMN	32 mm	#10		45 mm	195mm	93 mm
EL36P13LMN	36 mm	#11	35M	50 mm	210mm	99 mm
EL40P13LMN	40 mm			55 mm	224mm	106 mm


Table 2/2			
Catalog Number	Bar Depth (BD)	Thread Size (TS)	Unit Weight
EL10P13LMN	18mm	M18	0.21 kg
EL12P13LMN	19mm	M18	0.21 kg
EL14P13LMN	21mm	M18	0.21 kg
EL16P13LMN	24mm	M22	0.34 kg
EL18P13LMN	29mm	M24	0.43 kg
EL20P13LMN	35mm	M26	0.64 kg
EL22P13LMN	37mm	M31	0.96 kg
EL25P13LMN	40mm	M34	1.11 kg
EL28P13LMN	42mm	M37	1.42 kg

Catalog Number	Bar Depth (BD)	Thread Size (TS)	Unit Weight
EL32P13LMN	45mm	M42	2.07 kg
EL36P13LMN	52mm	M46	2.65 kg
EL40P13LMN	57mm	M53	3.55 kg

## ADDITIONAL PRODUCT DETAILS

Bar dimensions and weights listed may vary by region. Coupler sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**