

Varistar CP Steel Door, Perforated With 1-Point Locking, Key Plate Only, RAL 7021, 29 U, 1400H 800W

Power Utilities

CATALOG NUMBER

21630-510



Varistar CP Perforated Steel Door Single Point Locking for IP 20 applications.

FEATURES

Perforated steel door with single point locking for IP 20 protection class

Lever handle with built-in push button

Opening angle 180°

Key lock cover

PRODUCT ATTRIBUTES

Product Type: Cabinet Door

Product Family: Varistar CP

Type: Steel Door, Perforated

Works With: Varistar CP

Locking Type: Single Point Locking

Color: Black Grey

Color Code: RAL 7021

Rack Height: 29 U

Height: 1400 mm

Width: 800 mm

Protection Rating: IP20

Complies With: IEC 61587-1

ADDITIONAL PRODUCT DETAILS

Please order lever handle and DIN profile half cylinder separately.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE