

Rack Safety Plus, 3 U, 400 V AC, Cable

CATALOG NUMBER

21270-012



The nVent SCHROFF Rack Safety Plus unit is a 19" power distribution unit used to supply AC mains power to electrical or electronic devices as a central power switch. In addition it is equipped with an emergency stop function.

CERTIFICATIONS



FEATURES

19", 3 U Power Distribution Unit with Emergency Stop function

Supplies AC mains power to electrical or electronic devices as a central power switch

400 V 3-phase or 230 V 1-phase mains input with mains fuses

AC outputs with different connector types, switched by ON/OFF switch

Permanent AC Outputs (Service)

All outputs are protected by circuit breakers

The emergency stop function meets the requirements of EN 60947-5-1 and EN 60204-1 and is vandalism-proof

An additional external emergency stop push button can be connected to the system

PRODUCT ATTRIBUTES

Product Type: Power Distributor

Works With: Varistar CP; Novastar

Function: Emergency Stop

Input Voltage AC: 400V

Number of Phases: 3

EMC Filter: No

Surge Arrester: No

Inrush Current Limiter: No

Residual Current Device: Yes

Circuit Breaker Cover: No

Rack Height: 3U

Socket Type: IEC C13; IEC C13 LOCK

Accessory Type: Power distribution accessories

Net Weight: 12kg

Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

For exact configuration of optional features and example configuration please refer to the item(s) delivered table.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE