

2HPS Two Hole Pipe Strap



FEATURES

Light duty support of pipe

Attaches directly to the face of a horizontal or vertical structural member

SPECIFICATIONS


Finish: Pregalvanized

Material: Steel

Table 1/1										
Catalog Number	Article Number	NB/DN	Outer Diameter (OD)	Hole Size (HS)	Width (W)	Thickness (T)				
008060EG	400684	50	60.3 mm	7 mm	20 mm	1 mm				
008021EG	400679	15	21.3 mm	7 mm	20 mm	1 mm				
008034EG	400681	25	33.7 mm	7 mm	20 mm	1 mm				
008042EG	400682	32	42.4 mm	7 mm	20 mm	1 mm				
008017EG	400678	10	17.2 mm	7 mm	20 mm	1 mm				
008048EG	400683	40	48.3 mm	7 mm	20 mm	1 mm				

CatalogNumber	Article Number	NB/DN	Outer Diameter (OD)	Hole Size (HS)	Width (W)	Thickness (T)
008027EG	400680	20	26.9 mm	7 mm	20 mm	1 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN

ILSCO SCHROFF

TRACHTE



©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.