

Hex Nut



FEATURES

Internally threaded with a hex drive for many applications

SPECIFICATIONS

Table 1/1										
Catalog Number	Article Number	Material	Finish	Rod Size	Thickness	Wire Size				
010M6	592040	Steel	Electrogalvaniz ed	M6	5 mm	10 mm				
010M8S4	592140	Stainless Steel 304 (EN 1.4301)		M8	6.5 mm	13 mm				
010M8	592050	Steel	Electrogalvaniz ed	M8	6.5 mm	13 mm				
010M10HD	592065	Steel	Hot-Dip Galvanized	M10	8 mm	17 mm				
010M10S4	592150	Stainless Steel 304 (EN 1.4301)		M10	8 mm	17 mm				
010M12HD	592075	Steel	Hot-Dip Galvanized	M12	10 mm	19 mm				
010M12S4	592160	Stainless Steel 304 (EN 1.4301)		M12	10 mm	19 mm				

CatalogNumber	Article Number	Material	Finish	Rod Size	Thickness	Wire Size
010M12	592070	Steel	Electrogalvaniz ed	M12	10 mm	19 mm
010M16	400444	Steel	Electrogalvaniz ed	M16	13 mm	24 mm
010M10	592060	Steel	Electrogalvaniz ed	M10		

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793 Europe

Germany: 800 1890272 Other Countries: +31 13 5835404 APAC

Shanghai: + 86 21 2412 1618/19 Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE



©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.