

Aircraft Grounding Receptacle with Bar Attachment Point



FEATURES

Castings for use in static grounding systems of refueling areas

Suitable as a combination tie down and static ground point

Easily connected to grounding system conductor and/or ground rods

Designed for simple installation with flush paved surfaces

Compatible with nVent ERICO Cadweld connections

SPECIFICATIONS

Material: Phosphor Bronze

Table 1/1

Catalog Number	Article Number	Diameter 1 (Ø1)	Diameter 2 (Ø2)	Depth (D)	Attachment Point (AP)	Connection Type
B166	165220	98 mm	88.9 mm	133.35mm	19 mm Diameter Bar	RA, RB
B167	165230	120 mm	112 mm	184.2mm	38 mm Diameter Bar	RA, RB

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE