

# Document Pockets For Floor Standing Enclosures, DRBS



The stainless steel 316L document pocket can accommodate binders and other documents, and it is attached with screws, which provides a good solution when the enclosure is exposed to high temperatures, for example.

## FEATURES

Description: A large steel document pocket fixed directly onto the door frame. Usable depth: 68 mm.

Finish: 400 pre-grained stainless steel.

Pack quantity: 1 piece with mounting accessories.

The document pocket offers a strong fixation to the enclosure due to the installation method and material

The document pockets screw fixation provides a good solution in environments where an adhesive fixation will not work, e.g. when exposed to high temperatures

SPECIFICATIONS

Finish: Brushed  
Material: Stainless Steel 316L

| Table 1/1      |        |       |       |                             |                |            |
|----------------|--------|-------|-------|-----------------------------|----------------|------------|
| Catalog Number | Height | Width | Depth | Enclosure Material          | Product Family | Quick Ship |
| DRBS03030-316L | 272mm  | 300mm | 68mm  | Mild Steel, Stainless Steel | Free-Standing  | No         |
| DRBS1000-316L  | 272mm  | 845mm | 70mm  | Mild Steel, Stainless Steel | Free-Standing  | No         |
| DRBS0800-316L  | 272mm  | 645mm | 70mm  | Mild Steel, Stainless Steel | Free-Standing  | No         |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE