

# Ventilated Top Cable Cover, CRB



Up to four ventilation fans can be mounted on this roof plate, which means that the enclosure can be cooled in incremental steps, depending on the number of fans fitted. Brushes fitted to the cable openings allow for different cable diameters to be installed easily.

## FEATURES

Description: For cable entry on three sides in combination with ventilation. Cable openings provided with brushes. To mount closing plates DFC or inside mounting of (maximum 4) DFN01 ventilation fans.

Material: 1.5 mm steel plate.

Finish: RAL 7035 structured powder coating.

Pack quantity: 1 piece with brushes and mounting accessories.

Mounting requirements: Add DFN ventilation fans or DFC closing plates.

The brushes fitted to the cable openings allow different cable diameters to be installed in the field at the same time

It is recommended to install exhaust filters in the bottom of the enclosure to let air circulate properly

The cut-outs must be covered by either ventilation fans, DFN, or cover plates, DFC, depending on the amount of cooling required

For cable entry on three sides in combination with ventilation

Cable openings provided with brushes

To mount closing plates DFC or inside mounting of (maximum 4) DFN01 ventilation fans

Mounting requirements: Add DFN ventilation fans or DFC closing plates

SPECIFICATIONS

**Thickness:** 1.5mm  
**Color:** Light Gray  
**Material:** Mild Steel  
**Finish:** Powder Coated  
**Color Code:** RAL 7035

| Table 1/1      |        |       |       |                      |                    |            |
|----------------|--------|-------|-------|----------------------|--------------------|------------|
| Catalog Number | Height | Width | Depth | Cable Entry Quantity | Enclosure Material | Quick Ship |
| CRB0808R5      | 17mm   | 800mm | 800mm | 6                    | Mild Steel         | No         |
| CRB0806R5      | 17mm   | 800mm | 600mm | 4                    | Mild Steel         | No         |
| CRB0608R5      | 17mm   | 600mm | 800mm | 6                    | Mild Steel         | No         |
| CRB0606R5      | 17mm   | 600mm | 600mm | 4                    | Mild Steel         | No         |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE