

# EuropacPRO 19" Subrack Kit for Backplane, Light, Unshielded

## Power Utilities

Non-EMC shielded subrack for backplane mounting, light version.



## CERTIFICATIONS



## FEATURES

Subrack with side panel type L ("light") with integrated 19" support brackets

Horizontal rail type "light"

Aluminum construction

Rear horizontal rails for backplane mounting with insulation strip

Installed load up to 7.5 kg

Supplied as space-saving flat-pack

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Modifications such as cutouts, different finishes or dimensions available

## SPECIFICATIONS

Table 1/2

| Catalog Number | Rack Height | Depth  | Package Quantity | For Mounting | Board Depth            | Handle Included |
|----------------|-------------|--------|------------------|--------------|------------------------|-----------------|
| 24564-131      | 3 U         | 175 mm | 1                | Backplane    | 160 mm                 | No              |
| 24564-132      | 3 U         | 235 mm | 1                | Backplane    | 160 mm, 220 mm         | No              |
| 24564-133      | 3 U         | 295 mm | 1                | Backplane    | 160 mm, 220 mm, 280 mm | No              |
| 24564-431      | 6 U         | 175 mm | 1                | Backplane    | 160 mm                 | No              |
| 24564-432      | 6 U         | 235 mm | 1                | Backplane    | 160 mm, 220 mm         | No              |
| 24564-433      | 6 U         | 295 mm | 1                | Backplane    | 160 mm, 220 mm, 280 mm | No              |

Table 2/2

| Catalog Number | Mounting | Complies With                                 | EMC Shielding | Product Type    | Rack Width | Static Load |
|----------------|----------|-----------------------------------------------|---------------|-----------------|------------|-------------|
| 24564-131      | Rack     | IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1 | No            | Subrack/Chassis | 84 HP      | 7.5 kgf     |
| 24564-132      | Rack     | IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1 | No            | Subrack/Chassis | 84 HP      | 7.5 kgf     |
| 24564-133      | Rack     | IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1 | No            | Subrack/Chassis | 84 HP      | 7.5 kgf     |
| 24564-431      | Rack     | IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1 | No            | Subrack/Chassis | 84 HP      | 7.5 kgf     |
| 24564-432      | Rack     | IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1 | No            | Subrack/Chassis | 84 HP      | 7.5 kgf     |
| 24564-433      | Rack     | IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1 | No            | Subrack/Chassis | 84 HP      | 7.5 kgf     |

## ADDITIONAL PRODUCT DETAILS

---

Subrack is not prepared for shielding, retrofit for protection class IP 20 possible

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**