

EuropacPRO Cover Plate for Bolting to Rugged Side Panel

Power Utilities



A cover plate is used for electromagnetic shielding or as mechanical protection.

CERTIFICATIONS



FEATURES

Perforation degree 58%

SPECIFICATIONS

Table 1/2

Catalog Number	Depth	Package Quantity	Product Family	Product Type	Rack Width	Type
24568-036	277.75 mm	1	EuropacPRO	Cover Plate	84 HP	Perforated
24568-012	295 mm	1	EuropacPRO	Cover Plate	84 HP	Perforated
24568-008	235 mm	1	EuropacPRO	Cover Plate	84 HP	Perforated

CatalogNumber	Depth	Package Quantity	Product Family	Product Type	Rack Width	Type
24568-032	275 mm	1	EuropacPRO	Cover Plate	84 HP	Perforated
24568-004	175 mm	1	EuropacPRO	Cover Plate	84 HP	Perforated
24568-016	295 mm	1	EuropacPRO	Cover Plate	84 HP	Perforated
24568-020	355 mm	1	EuropacPRO	Cover Plate	84 HP	Perforated

Table 2/2

Catalog Number	Works With	Package Unit	Torque
24568-036	Subracks	Pair	2.1 N·m
24568-012	Subracks	Pair	2.1 N·m
24568-008	Subracks	Pair	2.1 N·m
24568-032	Subracks	Pair	2.1 N·m
24568-004	Subracks	Pair	2.1 N·m
24568-016	Subracks	Pair	2.1 N·m
24568-020	Subracks	Pair	2.1 N·m

ADDITIONAL PRODUCT DETAILS

A top cover locking mechanism is optionally available that also fixes the top cover in the front and rear guide rail.

4 stainless steel EMC contact strips per subrack are required for shielding, please order separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE