

Front Panel, Flat, Refrofit Shielding, D-Sub Cutouts

Power Utilities



Flat front panel with cutout for D-Sub connectors.
Shieldable for stainless steel EMC gasket.

CERTIFICATIONS



FEATURES

For stainless steel EMC gasket

Aluminum, 2.5 mm, front anodized, conductive

SPECIFICATIONS

Table 1/3						
Catalog Number	Package Quantity	Mounting	Front Finish	Rear Finish	Treated Edges	Complies With

30118-348	5	Screw-on Front	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10
30118-349	5	Screw-on Front	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10
30118-350	5	Screw-on Front	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10
30118-351	5	Screw-on Front	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10
30118-352	5	Screw-on Front	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10
30118-353	5	Screw-on Front	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10
30118-354	5	Screw-on Front	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10

Table 2/3

Catalog Number	EMC Shielding	Height	Material	Product Type	Rack Height	Rack Width
30118-348	No (Retrofittable)	128.4 mm	Aluminum	Front Panel	3 U	4 HP
30118-349	No (Retrofittable)	128.4 mm	Aluminum	Front Panel	3 U	4 HP
30118-350	No (Retrofittable)	128.4 mm	Aluminum	Front Panel	3 U	4 HP
30118-351	No (Retrofittable)	128.4 mm	Aluminum	Front Panel	3 U	4 HP
30118-352	No (Retrofittable)	128.4 mm	Aluminum	Front Panel	3 U	4 HP
30118-353	No (Retrofittable)	128.4 mm	Aluminum	Front Panel	3 U	4 HP
30118-354	No (Retrofittable)	128.4 mm	Aluminum	Front Panel	3 U	4 HP

Table 3/3

Catalog Number	Type	Width
----------------	------	-------

30118-348	Front Panel without Handle	20 mm
30118-349	Front Panel without Handle	20 mm
30118-350	Front Panel without Handle	20 mm
30118-351	Front Panel without Handle	20 mm
30118-352	Front Panel without Handle	20 mm
30118-353	Front Panel without Handle	20 mm
30118-354	Front Panel without Handle	20 mm

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

Delivery is in standard pack multiples. Pricing is per individual item.

Please order stainless steel EMC gasket separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE