


Front Panel, Flat, Unshielded, D-Sub Cutouts

Power Utilities



Flat front panel with cutout for D-Sub connectors.
Unshielded version.

CERTIFICATIONS



FEATURES

Non-shielded version

Aluminum, 2.5 mm, front anodized, rear conductive

SPECIFICATIONS

Table 1/3						
Catalog Number	Package Quantity	Mounting	Front Finish	Rear Finish	Treated Edges	Complies With
30118-346	5	Screw-on Front	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10

CatalogNumber	Package Quantity	Mounting	Front Finish	Rear Finish	Treated Edges	Complies With
30118-344	5	Screw-on Front	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10
30118-345	5	Screw-on Front	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10
30118-347	5	Screw-on Front	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10
30118-341	5	Screw-on Front	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10
30118-343	5	Screw-on Front	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10
30118-342	5	Screw-on Front	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10

Table 2/3

Catalog Number	EMC Shielding	Height	Material	Product Type	Rack Height	Rack Width
30118-346	No	128.4 mm	Aluminum	Front Panel	3 U	4 HP
30118-344	No	128.4 mm	Aluminum	Front Panel	3 U	4 HP
30118-345	No	128.4 mm	Aluminum	Front Panel	3 U	4 HP
30118-347	No	128.4 mm	Aluminum	Front Panel	3 U	4 HP
30118-341	No	128.4 mm	Aluminum	Front Panel	3 U	4 HP
30118-343	No	128.4 mm	Aluminum	Front Panel	3 U	4 HP
30118-342	No	128.4 mm	Aluminum	Front Panel	3 U	4 HP

Table 3/3

Catalog Number	Type	Width
30118-346	Front Panel without Handle	20 mm

Catalog Number	Type	Width
30118-344	Front Panel without Handle	20 mm
30118-345	Front Panel without Handle	20 mm
30118-347	Front Panel without Handle	20 mm
30118-341	Front Panel without Handle	20 mm
30118-343	Front Panel without Handle	20 mm
30118-342	Front Panel without Handle	20 mm

ADDITIONAL PRODUCT DETAILS

Delivery is in standard pack multiples. Pricing is per individual item.

Please order fixing material (sleeves, collar screws) separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE