

C-GW Cable Protection Plate



FEATURES

Cable protection plate

Used with nVent CADDY C-EC, C-EU, C-ERU and C-ES products

SPECIFICATIONS

Material: Polyethylene

Table 1/1

Catalog Number	Article Number	Outer Diameter	Length
C12GW	337800	9 - 12 mm	40mm
C16GW	337810	13 - 16 mm	40mm
C20GW	337820	17 - 20 mm	40mm
C24GW	337830	21 - 24 mm	40mm
C28GW	337840	25 - 28 mm	40mm
C32GW	337850	29 - 32 mm	40mm
C36GW	337860	33 - 36 mm	40mm

Catalog Number	Article Number	Outer Diameter	Length
C40GW	337870	37 - 40 mm	40mm
C48GW	337890	41 - 48 mm	40mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

