

Internal U-Shaped Coupler



SPECIFICATIONS

Material: Steel

Table 1/2

Catalog Number	Article Number	Finish	Strut Type	Length (L)	Screw Included	Screw Diameter (Sc)
ZU405PG	387805	Pregalvanized	A (41 x 41 mm)	250mm	Yes	6
ZUA404	387790	Hot-Dip Galvanized	C (21 x 41 mm)	250mm	No	
ZUA405	387800	Hot-Dip Galvanized	A (41 x 41 mm)	250mm	No	

Table 2/2

Catalog Number	Article Number	Screw Length (L)
ZU405PG	387805	12mm
ZUA404	387790	
ZUA405	387800	

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

