

Rubber Profile for Strut Channel



FEATURES

EPDM insulation profile to prevent contact between support and ventilation duct


Suitable for strut

Can be used with threaded rods up to M10

SPECIFICATIONS

Table 1/2								
Catalog Number	Article Number	Material	Temperature	Length (L)	Height (H)	Width (W)		
ISOSTRUT	335980	EPDM-SBR Rubber	-50 to 110 °C	20m	8 mm	42 mm		

Table 2/2						
Catalog Number	Article Number	Hole Size (HS)				
ISOSTRUT	335980	11 mm				



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO SCHROFF

TRACHTE



©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.