

Joint Bond Mold Pair Only, Signal, Head-Free Rail, Head Free Bond Terminal Style, Mold and Mold Cleaning Tool, 5/16" Bondstrand

Data Solutions

CATALOG NUMBER

SBB492



FEATURES

- Pair of replacement molds designed for the installation of jumper bonds to the head of the rail
- Connection is made within the confines of the splice plate

PRODUCT ATTRIBUTES

- Material: Graphite
- Rail Type: Head-Free Rail
- Bond Terminal Style: Head Free
- Product: Mold and Mold Cleaning Tool
- Conductor Size: 5/16" Bondstrand
- Conductor Outer Diameter, Nominal: 7.94mm
- Welder Style: T6; T7
- Mold Only: No
- Replacement Mold: SBB492M
- Welding Material: SB32 x 2, Sold Separately

Frame: SBB492F, Sold Separately

Conductor Sleeve: SBS09C x 2, Sold Separately

Bond Clip: B194D x 2, Sold Separately

Hammer Die: SBD51, Sold Separately

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE