

Arc Weldable Bond



FEATURES

19-strand concentric cable flash-welded to steel rod for a bonding connection to structural steel and to rebar

Economical alternative to exothermic welding when only a few connections need to be made and an arc welder is available on site

Rod is sized to match the ampacity of the cable for fault currents

SPECIFICATIONS

Material: Copper,Steel

Table 1/1

Catalog Number	Conductor Size	Cable Length	Rod Size	Rod Length
EWB2G9164	2/0 Stranded	1.2m	14.3mm	203mm
EWB2L584	3/0 Stranded	1.2m	15.9mm	203mm
EWB2Q344	4/0 Stranded	1.2m	19.1mm	203mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE