

# Joint Bond Mold Only, Power



## FEATURES

Replacement mold designed for the installation of jumper bonds to the head of the rail

Connection is made within the confines of the splice plate

## SPECIFICATIONS

**Bond Terminal Style:** C

**Material:** Graphite

Table 1/1

| Catalog Number | Article Number | Rail Type                       | Conductor Size              | Conductor Outer Diameter, Nominal | Orientation |
|----------------|----------------|---------------------------------|-----------------------------|-----------------------------------|-------------|
| MRR50D         | 547900         | UIC54, UIC60                    | 50 mm <sup>2</sup> Stranded | 9.27mm                            | Left Hand   |
| MRR50G         | 547910         | UIC54, UIC60                    | 50 mm <sup>2</sup> Stranded | 9.27mm                            | Right Hand  |
| PBCS6CWPRHM    |                | 85 lb to 141 lb T-Rail Sections | 3/0 Composite               | 14.53mm                           | Right Hand  |
| PBCS6CWPLHM    |                | 85 lb to 141 lb T-Rail Sections | 3/0 Composite               | 14.53mm                           | Left Hand   |
| PBC2WRHM       |                | 85 lb to 141 lb T-Rail Sections | 250 kcmil Ropelay           | 19.05mm                           | Right Hand  |
| PBC2WLHM       |                | 85 lb to 141 lb T-Rail Sections | 250 kcmil Ropelay           | 19.05mm                           | Left Hand   |

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**