

# Front Panel, Unshielded, Cut Outs for Coax Connectors

## Power Utilities



Aluminum, 2.5 mm, front anodized, conductive, unshielded version.

## CERTIFICATIONS



## FEATURES

Aluminum, 2.5 mm, front anodized, conductive

3 U, 4 HP

## SPECIFICATIONS

Table 1/3

| Catalog Number | Type                       | Mounting       | EMC Shielding | Material | Front Finish | Rear Finish |
|----------------|----------------------------|----------------|---------------|----------|--------------|-------------|
| 30118-355      | Front Panel without Handle | Screw-on Front | No            | Aluminum | Anodized     | Conductive  |

Table 2/3

| Catalog Number | Treated Edges | Rack Height | Height   | Rack Width | Width | Complies With                   |
|----------------|---------------|-------------|----------|------------|-------|---------------------------------|
| 30118-355      | No            | 3 U         | 128.4 mm | 4 HP       | 20 mm | IEC 60297-3-101, IEEE 1101.1/10 |

Table 3/3

| Catalog Number | Package Quantity |
|----------------|------------------|
| 30118-355      | 5                |

## ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**