

Novastar Cabinet Without Door and Rear Panel



Aluminum frame cabinets with attractive design, ideally suited for general electronics, test and measurement, audio/video and broadcasting applications.

CERTIFICATIONS



FEATURES

Static load-carrying capacity up to 400 kg (see specification table)

Type of protection IP 20

Cabinet width only 553 mm

Flush cladding parts

All uprights (front and rear) with 19" cut-outs

Colors: RAL 7021 or color combination RAL 7021/ RAL 7035

Bolted, die-cast frame with Al extrusions

Without door and rear panel

SPECIFICATIONS

Frame Material:	Aluminum
Material:	Aluminum; Steel
Product Type:	Cabinet
Complies With:	IEC 60297-3-100

Table 1/3

Catalog Number	Rack Height	Frame Color	Height	Frame Color Code	Cladding Material	Width
15230-001	9U	Black Grey	456mm	RAL 7021	Steel	553mm
15230-002	12U	Black Grey	589mm	RAL 7021	Steel	553mm
15230-003	12U	Black Grey	589mm	RAL 7021	Steel	553mm
15230-004	16U	Black Grey	767mm	RAL 7021	Steel	553mm
15230-005	16U	Black Grey	767mm	RAL 7021	Steel	553mm
15230-006	20U	Black Grey	945mm	RAL 7021	Steel	553mm
15230-007	20U	Black Grey	945mm	RAL 7021	Steel	553mm
15230-008	20U	Black Grey	945mm	RAL 7021	Steel	553mm
15230-009	25U	Black Grey	1167mm	RAL 7021	Steel	553mm
15230-010	25U	Black Grey	1167mm	RAL 7021	Steel	553mm
15230-011	34U	Black Grey	1567mm	RAL 7021	Steel	553mm
15230-012	34U	Black Grey	1567mm	RAL 7021	Steel	553mm
15230-013	38U	Black Grey	1745mm	RAL 7021	Steel	553mm
15230-014	38U	Black Grey	1745mm	RAL 7021	Steel	553mm
15230-015	43U	Black Grey	1967mm	RAL 7021	Steel	553mm
15230-016	43U	Black Grey	1967mm	RAL 7021	Steel	553mm
15230-017	47U	Black Grey	2145mm	RAL 7021	Steel	553mm
15230-018	47U	Black Grey	2145mm	RAL 7021	Steel	553mm

CatalogNumber	Rack Height	Frame Color	Height	Frame Color Code	Cladding Material	Width
16230-001	9U	Black Grey	456mm	RAL 7021	Steel	553mm
16230-002	12U	Black Grey	589mm	RAL 7021	Steel	553mm
16230-003	12U	Black Grey	589mm	RAL 7021	Steel	553mm
16230-004	16U	Black Grey	767mm	RAL 7021	Steel	553mm
16230-005	16U	Black Grey	767mm	RAL 7021	Steel	553mm
16230-006	20U	Black Grey	945mm	RAL 7021	Steel	553mm
16230-007	20U	Black Grey	945mm	RAL 7021	Steel	553mm
16230-008	20U	Black Grey	945mm	RAL 7021	Steel	553mm
16230-009	25U	Black Grey	1167mm	RAL 7021	Steel	553mm
16230-010	25U	Black Grey	1167mm	RAL 7021	Steel	553mm
16230-011	34U	Black Grey	1567mm	RAL 7021	Steel	553mm
16230-012	34U	Black Grey	1567mm	RAL 7021	Steel	553mm
16230-013	38U	Black Grey	1745mm	RAL 7021	Steel	553mm
16230-014	38U	Black Grey	1745mm	RAL 7021	Steel	553mm
16230-015	43U	Black Grey	1967mm	RAL 7021	Steel	553mm
16230-016	43U	Black Grey	1967mm	RAL 7021	Steel	553mm
16230-017	47U	Black Grey	2145mm	RAL 7021	Steel	553mm
16230-018	47U	Black Grey	2145mm	RAL 7021	Steel	553mm

Table 2/3

Catalog Number	Cladding Color	Depth	Static Load	Cladding Color Code	Package Quantity	Finish
15230-001	Black Grey	600mm	200kg	RAL 7021	1	Powder Coated
15230-002	Black Grey	500mm	200kg	RAL 7021	1	Powder Coated
15230-003	Black Grey	600mm	200kg	RAL 7021	1	Powder Coated
15230-004	Black Grey	500mm	200kg	RAL 7021	1	Powder Coated
15230-005	Black Grey	600mm	200kg	RAL 7021	1	Powder Coated
15230-006	Black Grey	500mm	200kg	RAL 7021	1	Powder Coated
15230-007	Black Grey	600mm	200kg	RAL 7021	1	Powder Coated
15230-008	Black Grey	800mm	200kg	RAL 7021	1	Powder Coated
15230-009	Black Grey	600mm	200kg	RAL 7021	1	Powder Coated
15230-010	Black Grey	800mm	200kg	RAL 7021	1	Powder Coated
15230-011	Black Grey	600mm	400kg	RAL 7021	1	Powder Coated
15230-012	Black Grey	800mm	400kg	RAL 7021	1	Powder Coated
15230-013	Black Grey	600mm	400kg	RAL 7021	1	Powder Coated
15230-014	Black Grey	800mm	400kg	RAL 7021	1	Powder Coated
15230-015	Black Grey	600mm	400kg	RAL 7021	1	Powder Coated
15230-016	Black Grey	800mm	400kg	RAL 7021	1	Powder Coated
15230-017	Black Grey	600mm	400kg	RAL 7021	1	Powder Coated
15230-018	Black Grey	800mm	400kg	RAL 7021	1	Powder Coated

CatalogNumber	Cladding Color	Depth	Static Load	Cladding Color Code	Package Quantity	Finish
16230-001	Light Grey	600mm	200kg	RAL 7035	1	Powder Coated
16230-002	Light Grey	500mm	200kg	RAL 7035	1	Powder Coated
16230-003	Light Grey	600mm	200kg	RAL 7035	1	Powder Coated
16230-004	Light Grey	500mm	200kg	RAL 7035	1	Powder Coated
16230-005	Light Grey	600mm	200kg	RAL 7035	1	Powder Coated
16230-006	Light Grey	500mm	200kg	RAL 7035	1	Powder Coated
16230-007	Light Grey	600mm	200kg	RAL 7035	1	Powder Coated
16230-008	Light Grey	800mm	200kg	RAL 7035	1	Powder Coated
16230-009	Light Grey	600mm	200kg	RAL 7035	1	Powder Coated
16230-010	Light Grey	800mm	200kg	RAL 7035	1	Powder Coated
16230-011	Light Grey	600mm	400kg	RAL 7035	1	Powder Coated
16230-012	Light Grey	800mm	400kg	RAL 7035	1	Powder Coated
16230-013	Light Grey	600mm	400kg	RAL 7035	1	Powder Coated
16230-014	Light Grey	800mm	400kg	RAL 7035	1	Powder Coated
16230-015	Light Grey	600mm	400kg	RAL 7035	1	Powder Coated
16230-016	Light Grey	800mm	400kg	RAL 7035	1	Powder Coated
16230-017	Light Grey	600mm	400kg	RAL 7035	1	Powder Coated
16230-018	Light Grey	800mm	400kg	RAL 7035	1	Powder Coated

Table 3/3

Catalog Number	Quick Ship
15230-001	No
15230-002	No
15230-003	No
15230-004	No
15230-005	No
15230-006	No
15230-007	No
15230-008	No
15230-009	No
15230-010	No
15230-011	No
15230-012	No
15230-013	No
15230-014	No
15230-015	No
15230-016	No
15230-017	No
15230-018	No

Catalog Number	Quick Ship
16230-001	No
16230-002	No
16230-003	No
16230-004	No
16230-005	No
16230-006	No
16230-007	No
16230-008	No
16230-009	No
16230-010	No
16230-011	No
16230-012	No
16230-013	No
16230-014	No
16230-015	No
16230-016	No
16230-017	No
16230-018	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE