

# PSU 19" AC/DC Maxpower 100 W, Single, Adjustable



Pluggable 19" Power Supplies with H15 connector for fanless applications. With wide range AC input and a single, adjustable output voltage.

## CERTIFICATIONS



## FEATURES

Wide input voltage range 90 ... 264 VAC and 100 ... 360 VDC with active Power Factor Correction (PFC)

1 output voltage

Signalling: Output voltage OK

Wide adjustment range of output voltage

Integrated decoupling diode for redundancy

Active Current Share Bus (CSB)

## SPECIFICATIONS

Table 1/2

| Catalog Number | Type              | Input Voltage AC | Input Voltage DC | Power | Number of Output Voltages | Voltage 1 |
|----------------|-------------------|------------------|------------------|-------|---------------------------|-----------|
| 13100-134      | 19" Switched-Mode | 90 – 264V        |                  | 102W  | 1                         | 16V       |

| CatalogNumber | Type              | Input Voltage AC | Input Voltage DC | Power | Number of OutputVoltages | Voltage 1 |
|---------------|-------------------|------------------|------------------|-------|--------------------------|-----------|
| 13100-133     | 19" Switched-Mode | 90 – 264V        | 100 – 360V       | 100W  | 1                        | 4.5V      |

Table 2/2

| Catalog Number | Current 1 | Rack Height | Rack Width | Depth    | Package Quantity | Quick Ship |
|----------------|-----------|-------------|------------|----------|------------------|------------|
| 13100-134      | 3.4A      | 3U          | 6HP        | 171.93mm | 1                | No         |
| 13100-133      | 5.9A      | 3U          | 6HP        | 171.93mm | 1                | No         |

## ADDITIONAL PRODUCT DETAILS

Please order front panel separately.

Output data at mains voltage 190 V AC, Ta= 0 ... 50 °C.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**