

EM-MR Conduit to Flange Clip with Retainer



FEATURES

Only one piece to install

Fast hammer-on installation

Pre-riveted retainer strap is easily bent into position

SPECIFICATIONS

Finish: nVent CADDY Armour

Material: Spring Steel

Table 1/1

Catalog Number	Outer Diameter	Flange Thickness	Static Load
CM24812M	18 - 30 mm	3.2 - 6.4 mm	330N
CM2416M	23.4 - 35 mm	3.2 - 6.4 mm	330N
CM5816M	23.4 - 35 mm	7.9 - 12.7 mm	330N
CM58812M	18 - 30 mm	7.9 - 12.7 mm	330N
CM912812M	18 - 30 mm	14.3 - 19.1 mm	330N
CM91216M	23.4 - 35 mm	14.3 - 19.1 mm	330N

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

