

# Heavy Duty T-Grid Box Hanger



## CERTIFICATIONS



## FEATURES

Quickly mounts a box to T-grid

Adjustable height for various electrical box depths

Mounts flush with face of tile

Installs by hand

Drop wire for independent support from clip and/or bar

Screws easily to tee bar for added stability

Supports multiple box installations

## SPECIFICATIONS

Table 1/1

| Catalog Number | Material            | Finish                            | Included Components | Length  | Box Depth  | Ultimate Static Load |
|----------------|---------------------|-----------------------------------|---------------------|---------|------------|----------------------|
| 512HD          | Steel, Spring Steel | Pregalvanized, nVent CADDY Armour | Mounting Clip       | 609.6mm | 38mm, 54mm | 220N                 |

ADDITIONAL PRODUCT DETAILS

Standard bar mounts 2 1/8" box. Break off tabs for 1 1/2" deep box. Mounts flush with face of tile.

512HDEEP Series with additional 512HDXT mounts 2 1/8" deep box with 1 1/2" extension ring.

Not permitted for paddle fans.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE

