

nVent CADDY Speed Link SLK with Wedge Anchor



FEATURES

Complete system includes wire, locking device and wedge anchor from fischerwerke GmbH &Co. KG

Quickly and easily attaches into cracked and non-cracked concrete

No special tools required

ETA 06/0175 approval available from fischerwerke GmbH &Co. KG

SPECIFICATIONS

Static Load Safety Factor:	5:1
Drill Bit Diameter:	6mm
Drill Hole Depth:	31mm
Finish:	Electrogalvanized
Material:	Steel;Polypropylene;Zinc Alloy
Embedment Depth:	25 mm Min

Table 1/2

Catalog Number	Article Number	Wire Rope Diameter	Wire Rope Length	Length (L)	Height (H)	Width (W)
SLK15L1WA6	196670	1.5 mm	1m	63.5mm	55 mm	19 mm
SLK15L2WA6	196671	1.5 mm	2m	54mm	55 mm	19 mm

CatalogNumber	Article Number	Wire Rope Diameter	Wire Rope Length	Length (L)	Height (H)	Width (W)
SLK15L5WA6	196673	1.5 mm	5m	63.5mm	55 mm	19 mm
SLK2L2WA6	196734	2 mm	2m	54mm	55 mm	19 mm
SLK2L3WA6	196735	2 mm	3m	54mm	55 mm	19 mm
SLK2L5WA6	196736	2 mm	5m	63.5mm	55 mm	19 mm
SLK3L2WA6	196723	3 mm	2m	63.5mm	62 mm	24 mm
SLK3L5WA6	196725	3 mm	5m	63.5mm	62 mm	24 mm

Table 2/2

Catalog Number	Article Number	Thickness (T)	Angle (a)	Static Load
SLK15L1WA6	196670	12.5 mm	90 ° Max	195N
SLK15L2WA6	196671	12.5 mm	90 ° Max	195N
SLK15L5WA6	196673	12.5 mm	90 ° Max	195N
SLK2L2WA6	196734	12.5 mm	90 ° Max	300N
SLK2L3WA6	196735	12.5 mm	90 ° Max	300N
SLK2L5WA6	196736	12.5 mm	90 ° Max	440N
SLK3L2WA6	196723	16 mm	90 ° Max	800N
SLK3L5WA6	196725	16 mm	90 ° Max	800N

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

