

Snap Close Conduit to Conduit Clamp



CERTIFICATIONS



FEATURES

Fast and easy assembly for lightweight loads

No screws or bolts required

SPECIFICATIONS

Finish: nVent CADDY Armour

Material: Spring Steel

Table 1/1

Catalog Number	Outer Diameter 1	Outer Diameter 2	Ultimate Static Load	Certifications
166M	30 - 35 mm	14 - 18 mm	440N	
16812M	30 - 35 mm	18 - 30 mm	440N	cUL, UL
1616M	25.4 mm Min	25.4 mm Min	440N	UL, cUL

Catalog Number	Outer Diameter 1	Outer Diameter 2	Ultimate Static Load	Certifications
1620M	30 - 35 mm	35 - 42 mm	440N	UL, cUL

ADDITIONAL PRODUCT DETAILS

For 14-2 through 12-3 MC/AC cable, use part 166M.

Total load of trapeze must not exceed 100 lb.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

