

Cable to Web of Rail Mold Only, Signal, 1" Tab Bond Terminal Style, 16 mm² Concentric, Right Hand

CATALOG NUMBER

SBB200YRH



FEATURES

Replacement mold designed for the installation of track circuits and jumper bonds to the neutral axis

PRODUCT ATTRIBUTES

Material: Graphite

Rail Type: 85 lb to 141 lb T-Rail Sections

Bond Terminal Style: 1" Tab

Conductor Size: 16 mm² Concentric

Conductor Outer Diameter, Nominal: 5.18mm

Welder Style: T21;TB5

Orientation: Right Hand

Mold Only: Yes

Welding Material: SB25 or SB25PLUSF80, Sold Separately

Handle Clamp: C105B, Sold Separately

Conductor Sleeve: SBS12C, Sold Separately

Bond Clip: S2659, Sold Separately

Hammer Die: SBD50, Sold Separately

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE