

Prefabricated Bonding Assembly



FEATURES

Prefabricated assembly includes rebar with an exothermic weld to copper conductor

Wire tie or weld rebar to construction steel before pouring concrete and route conductor pigtail to down lead or ground lead location

SPECIFICATIONS

Material: Copper;Steel

Table 1/1

Catalog Number	Conductor Type	Pigtail Length	Rebar Size, US	Length (L)	Unit Weight
LPP691	LPC122	1.52m	#4	457.2mm	1 kg
LPP692	LPC126R	1.52m	#4	457.2mm	1.33 kg
LPP693	LPC137	1.52m	#4	457.2mm	2 kg



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE