

Dual Thermostat



Two thermostats in one, the Dual Thermostat independently controls equipment heating and cooling systems.

INDUSTRY STANDARDS

cURus; File No. E164102

CSA File No. 215952

CE

FEATURES

Two thermostats; one normally closed (NC), red, and one normally open (NO), blue, in one casing

Wide adjustable temperature range (32 -140 F)

Thermostatic bimetallic sensor element

Connection is a 4-pole terminal for AWG 14 max (2.5 mm sq)

Mounting clip for 35-mm DIN rail

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Width	Depth	Material	Finish	Color
ADLTEMP	16451	50mm	46mm	Plastic	Smooth Matte	Light Gray

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE