

VPL Power-Limiting Heating Cable



nVent RAYCHEM VPL power-limiting trace heating cables are mainly used for process temperature maintenance applications that require steam cleaning, up to 455 °F/235 °C and withstand intermittent exposure to 500 °F/260 °C. VPL offers high power output at high temperatures, which can reduce the number of heating cables required and is hazardous area approved. Also suitable for freeze protection. The fluoropolymer outer jacket (-CT) provides high chemical resistance against aggressive organics and corrosives.

FEATURES

Efficient system design: high power output at elevated temperatures reduces heating cable required, flat P-T curve results in lower T start up and power equipment costs, longer circuit lengths due to larger cross section conductors

Maximum circuit length further increases when operating at higher voltages: reducing the number of circuits and power supply equipment

Fast installation: cut-to-length, multiple overlaps allowed, meter markings, user-friendly connections kits

Safe and efficient in operation: no overheating, uniform pipe temperatures, energy saving technology

Reliable during long life: 10 year product warranty available, maintenance free

SPECIFICATIONS

Max Continuous Exposure Temperature, Power Off:	260 °C
Max Cumulative Hours for Intermittent Exposure:	1000 h
Min Installation Temperature:	-60 °C
Ground Path Type:	Braid
Area Classification:	Non-Hazardous; Hazardous
Outer Jacket Material:	High Temperature Fluoropolymer

Table 1/1

Catalog Number	Item Name	Supply Voltage	Nominal Power Output @ 10°C, 230V	Nominal Power Output @ 10°C, 400V	Max Maintain or Continuous Exposure Temperature, Power On
068380-000	15VPL2-CT	200 – 277 V	45 W/m		230 °C

Catalog Number	Item Name	Supply Voltage	Nominal Power Output @ 10°C, 230V	Nominal Power Output @ 10°C, 400V	Max Maintain or Continuous Exposure Temperature, Power On
451828-000	5VPL2-CT	200 – 277 V	15 W/m		235 °C
589252-000	20VPL2-CT	200 – 240 V	61 W/m		150 °C
892652-000	10VPL2-CT	200 – 277 V	30 W/m		220 °C
P000000678	5VPL4-CT	400 – 480 V		12 W/m	230 °C
P000000679	10VPL4-CT	400 – 480 V		24 W/m	205 °C
P000000680	15VPL4-CT	400 – 480 V		36 W/m	170 °C
P000000681	20VPL4-CT	400 – 480 V		49 W/m	150 °C

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT