

# Front Panel, Unshielded, With Fastener Pin



Front panel with GND/earthing connection. The grounding can be done with a cable which fits to the fastener pin on the rear side of the panel.

## CERTIFICATIONS



## FEATURES

Enable grounding of the front area (protection class 1)

## SPECIFICATIONS

|                        |                            |
|------------------------|----------------------------|
| <b>Depth:</b>          | 2.5mm                      |
| <b>Rack Height:</b>    | 3U                         |
| <b>Material:</b>       | Aluminum                   |
| <b>Finish:</b>         | Anodized; Passivated       |
| <b>Accessory Type:</b> | Front panel                |
| <b>Product Type:</b>   | Front Panel                |
| <b>Type:</b>           | Front Panel without Handle |

Table 1/2

| Catalog Number | Rack Width | Package Quantity | Mounting       | Front Finish | Rear Finish | Treated Edges |
|----------------|------------|------------------|----------------|--------------|-------------|---------------|
| 20119-159      | 7HP        | 1                | Screw-on Front | Anodized     | Conductive  | No            |

| CatalogNumber | Rack Width | Package Quantity | Mounting       | Front Finish | Rear Finish | Treated Edges |
|---------------|------------|------------------|----------------|--------------|-------------|---------------|
| 20119-160     | 14HP       | 1                | Screw-on Front | Anodized     | Conductive  | No            |
| 20119-161     | 21HP       | 1                | Screw-on Front | Anodized     | Conductive  | No            |
| 20119-162     | 28HP       | 1                | Screw-on Front | Anodized     | Conductive  | No            |
| 20119-163     | 42HP       | 1                | Screw-on Front | Anodized     | Conductive  | No            |

Table 2/2

| Catalog Number | Complies With                      | EMC Shielding | Height  | Width   | Quick Ship |
|----------------|------------------------------------|---------------|---------|---------|------------|
| 20119-159      | IEC 60297-3-101,<br>IEEE 1101.1/10 | No            | 128.4mm | 35.2mm  | No         |
| 20119-160      | IEC 60297-3-101,<br>IEEE 1101.1/10 | No            | 128.4mm | 70.8mm  | No         |
| 20119-161      | IEC 60297-3-101,<br>IEEE 1101.1/10 | No            | 128.4mm | 106.3mm | No         |
| 20119-162      | IEC 60297-3-101,<br>IEEE 1101.1/10 | No            | 128.4mm | 141.9mm | No         |
| 20119-163      | IEC 60297-3-101,<br>IEEE 1101.1/10 | No            | 128.4mm | 213mm   | No         |

## ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**