

# Telescopic Slide Universal, Slim, 2 U

Slim Universal Telescopic Slide, 2 U.



## CERTIFICATIONS



## FEATURES

Rail width k = 9.7 mm, max. installation width of extension/drawer w = 429 mm

Lateral mounting on the 19" uprights (19" plane remains free for fixing the extension/drawer)

Locking at full extension

Static load-carrying capacity per pair 46 - 57 kg

Extension length > 110 %

## SPECIFICATIONS

|                      |                  |
|----------------------|------------------|
| <b>Material:</b>     | Steel            |
| <b>Product Type:</b> | Telescopic Slide |
| <b>Finish:</b>       | Zinc Plated      |

Table 1/1

| Catalog Number | Length | Package Quantity | Static Load | Type      | Quick Ship |
|----------------|--------|------------------|-------------|-----------|------------|
| 20110-071      | 356mm  | 2                | 57kg        | Universal | No         |

| Catalog Number | Length | Package Quantity | Static Load | Type      | Quick Ship |
|----------------|--------|------------------|-------------|-----------|------------|
| 20110-074      | 508mm  | 2                | 55kg        | Universal | No         |
| 20110-077      | 610mm  | 2                | 46kg        | Universal | No         |
| 20110-073      | 457mm  | 2                | 55kg        | Universal | No         |
| 20110-075      | 559mm  | 2                | 46kg        | Universal | No         |
| 20110-072      | 406mm  | 2                | 55kg        | Universal | No         |
| 20110-076      | 584mm  | 2                | 46kg        | Universal | No         |

## ADDITIONAL PRODUCT DETAILS

Universal telescopic Rails can also be fitted without additional components in non-standard applications, this also in other than 19" cabinets.

To mount on 19" plane please order assembly kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**