

Varistar Server Cabinet, RAL 7021



Server rack for high static load requirements, completely assembled and grounded including side by side kits.

CERTIFICATIONS



FEATURES

Static load-carrying capacity up to 1600 kg

Ingress protection class IP 20

Installation of different servers possible

Server cabinet with perforated doors, airflow rate 78 %

RAL 7021 (black grey)

SPECIFICATIONS

Table 1/3

Catalog Number	Type	Frame Material	Cladding Material	Frame Color	Frame Color Code	Cladding Color
10130-275	Side-by-Side	Steel	Steel	Black Grey	RAL 7021	Black Grey
10130-276	Side-by-Side	Steel	Steel	Black Grey	RAL 7021	Black Grey
10130-285	Side-by-Side	Steel	Steel	Black Grey	RAL 7021	Black Grey

CatalogNumber	Type	Frame Material	Cladding Material	Frame Color	Frame Color Code	Cladding Color
10130-286	Side-by-Side	Steel	Steel	Black Grey	RAL 7021	Black Grey
10130-279	Side-by-Side	Steel	Steel	Black Grey	RAL 7021	Black Grey
10130-280	Side-by-Side	Steel	Steel	Black Grey	RAL 7021	Black Grey
10130-289	Side-by-Side	Steel	Steel	Black Grey	RAL 7021	Black Grey
10130-290	Side-by-Side	Steel	Steel	Black Grey	RAL 7021	Black Grey
10130-283	Side-by-Side	Steel	Steel	Black Grey	RAL 7021	Black Grey
10130-284	Side-by-Side	Steel	Steel	Black Grey	RAL 7021	Black Grey
10130-293	Side-by-Side	Steel	Steel	Black Grey	RAL 7021	Black Grey
10130-294	Side-by-Side	Steel	Steel	Black Grey	RAL 7021	Black Grey
10130-234		Steel	Steel			
10130-235		Steel	Steel			
10130-232		Steel	Steel			
10130-233		Steel	Steel			

Table 2/3

Catalog Number	Cladding Color Code	Rack Height	Height	Width	Depth	Static Load
10130-275	RAL 7021	42U	2000mm	600mm	1000mm	1600kg
10130-276	RAL 7021	42U	2000mm	800mm	1000mm	1600kg
10130-285	RAL 7021	42U	2000mm	600mm	1200mm	1600kg

CatalogNumber	Cladding Color Code	Rack Height	Height	Width	Depth	Static Load
10130-286	RAL 7021	42U	2000mm	800mm	1200mm	1600kg
10130-279	RAL 7021	47U	2200mm	600mm	1000mm	1600kg
10130-280	RAL 7021	47U	2200mm	800mm	1000mm	1600kg
10130-289	RAL 7021	47U	2200mm	600mm	1200mm	1600kg
10130-290	RAL 7021	47U	2200mm	800mm	1200mm	1600kg
10130-283	RAL 7021	52U	2450mm	600mm	1000mm	1600kg
10130-284	RAL 7021	52U	2450mm	800mm	1000mm	1600kg
10130-293	RAL 7021	52U	2450mm	600mm	1200mm	1600kg
10130-294	RAL 7021	52U	2450mm	800mm	1200mm	1600kg
10130-234			2000mm	600mm	1200mm	
10130-235			2200mm	600mm	1200mm	
10130-232			2000mm	800mm	1200mm	
10130-233			2200mm	800mm	1200mm	

Table 3/3

Catalog Number	Certifications	Quick Ship
10130-275	RoHS	No
10130-276	RoHS	No
10130-285	RoHS	No
10130-286	RoHS	No

Catalog Number	Certifications	Quick Ship
10130-279	RoHS	No
10130-280	RoHS	No
10130-289	RoHS	No
10130-290	RoHS	No
10130-283	RoHS	No
10130-284	RoHS	No
10130-293	RoHS	No
10130-294	RoHS	No
10130-234		No
10130-235		No
10130-232		No
10130-233		No

ADDITIONAL PRODUCT DETAILS

Single cabinet can be combined with side-by-side cabinets and side panels.

Side panels not included and may be ordered separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE