

nVent CADDY Cat CM U-Hook, Strut Mount

Data Solutions



CERTIFICATIONS



FEATURES

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic

Integrated quick-attach T-nut allows U-Hooks to be quickly mounted to strut

System offers a convenient pathway for wires and cables

Specially designed U-Hooks have large-diameter, rounded support surfaces

Rounded edges help prevent over-bending and kinking of cables

Ideal for retrofit applications where cable runs need to be routed around existing building infrastructure

Compliant with NEC® and ANSI®/TIA structured cabling systems standards

SPECIFICATIONS

Finish:	Electrogalvanized
Included Components:	Quick-Attach T-Nut
Material:	Steel


Table 1/2

Catalog Number	Article Number	Cable Capacity, Cat 5e	Cable Capacity, Cat 6	Cable Capacity, Cat 6A	A	Area
CAT200CM	181982	450	350	215	203mm	533mm ²
CAT300CM	181984	700	525	325	304mm	812mm ²

Table 2/2

Catalog Number	Article Number	Hole Size (HS)	Static Load
CAT200CM	181982	9.5mm	440N
CAT300CM	181984	9.5mm	440N

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE