

# Rail Web Mold Clamp, Adjustable

## Data Solutions



### FEATURES

Adjusts for a wide span of uses including frogs and switches

Lightweight and easy to use

Can also be used on standard (single) rail

SBC105RR provides improved safety with non-sharp profiles and reflecting tape for high visibility

### SPECIFICATIONS

Table 1/1

| Catalog Number | Welder Style | Mold Size | Jaw Opening |
|----------------|--------------|-----------|-------------|
| PBC105P1       | T20          | 57 mm     | 600mm max   |
| SBC105RR       | T21          | 60 mm     | 648mm max   |
| PBC105P        | T20          | 89 mm     | 600mm max   |
| PBC105Q        | T20          | 89 mm     | 150mm max   |
| SBC105R        | T21          | 76 mm     | 648mm max   |

| Catalog Number | Welder Style | Mold Size | Jaw Opening |
|----------------|--------------|-----------|-------------|
| PBC105P2       | T20          | 76 mm     | 600mm max   |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE