

# Stamped U-Bolt Pipe Clamp



## CERTIFICATIONS



## FEATURES

Clamp for bonding of pipes and exhaust stacks to the lightning protection system

Listed to UL® 96

## SPECIFICATIONS


Table 1/2

| Catalog Number | Material                                           | Outer Diameter (OD) | Depth (D) | Height (H) | Width (W) | Unit Weight |
|----------------|----------------------------------------------------|---------------------|-----------|------------|-----------|-------------|
| LPA5966        | Aluminum,<br>Stainless Steel<br>304 (EN<br>1.4301) | 111.1 - 174.2<br>mm | 50.8mm    | 223.84 mm  | 211.15 mm | 0.34 kg     |
| LPA5964        | Aluminum,<br>Stainless Steel<br>304 (EN<br>1.4301) | 99.1 - 107.97<br>mm | 50.8mm    | 147.64 mm  | 158.75 mm | 0.34 kg     |
| LPC5966        | Copper,<br>Stainless Steel<br>304 (EN<br>1.4301)   | 111.1 - 174.2<br>mm | 50.8mm    | 223.84 mm  | 211.15 mm | 0.37 kg     |

| CatalogNumber | Material                                         | Outer Diameter (OD) | Depth (D) | Height (H) | Width (W) | Unit Weight |
|---------------|--------------------------------------------------|---------------------|-----------|------------|-----------|-------------|
| LPC5964       | Copper,<br>Stainless Steel<br>304 (EN<br>1.4301) | 99.1 - 117.47<br>mm | 50.8mm    | 147.64 mm  | 158.75 mm | 0.4 kg      |

| Table 2/2      |                                            |
|----------------|--------------------------------------------|
| Catalog Number | Certifications                             |
| LPA5966        | E202878-Combined_CoC, E202878-Combined_CoC |
| LPA5964        | E202878-Combined_CoC, E202878-Combined_CoC |
| LPC5966        |                                            |
| LPC5964        | E202878-Combined_CoC, E202878-Combined_CoC |

### DIAGRAMS



### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**