

PCR Perforated C-Shaped Profile



CERTIFICATIONS



FEATURES

Rapid assembly of all kinds of frameworks

High mechanical resistance

High corrosion resistance

Conforms to EN 60715 and DIN 46277

RoHS compliant

SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel

Table 1/2

Catalog Number	Article Number	Height (H)	Width (W)	Length (L)	Thickness (T)	A
PCR30X15-3M	557780	30 mm	15 mm	3000mm	1.5 mm	15 mm
PCR40X20-2M	557500	40 mm	20 mm	2000mm	1.5 mm	24 mm

CatalogNumber	Article Number	Height (H)	Width (W)	Length (L)	Thickness (T)	A
PCR35X35-2M	557520	35 mm	35 mm	2000mm	2 mm	16 mm
PCR35X35-3M	557790	35 mm	35 mm	3000mm	2 mm	16 mm

Table 2/2

Catalog Number	Article Number	B	C	D	Unit Weight
PCR30X15-3M	557780	7 mm	18 mm	8.2 mm	2.4 kg
PCR40X20-2M	557500	7 mm	18 mm	8.2 mm	2.5 kg
PCR35X35-2M	557520	7 mm	18 mm	8.2 mm	3 kg
PCR35X35-3M	557790	7 mm	18 mm	8.2 mm	4.5 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE