

# Reinforcing Steel Cleaning Brush



The reinforcing steel cleaning brush is used to prepare reinforcing steel for use with nVent LENTON Cadweld. The brush is designed to remove rust, mill scale, dirt and paint in as little as five seconds.

## FEATURES

Designed for use with a 3/4", heavy duty, low-speed drill (200-350 rpm)

Cleans reinforcing steel bar, including the bar end

## SPECIFICATIONS

**Material:** Steel

Table 1/1

| Catalog Number | Rebar Size, Metric | Rebar Size, US | Rebar Size, Canada | Diameter (Ø) | Length (L) |
|----------------|--------------------|----------------|--------------------|--------------|------------|
| RBW34311       | 36 mm              | #11            | 35M                | 114 mm       | 244mm      |
| RBW34318       | 57 mm              | #18            | 55M                | 127 mm       | 206mm      |
| RBW34314       | 43 mm              | #14            | 45M                | 127 mm       | 181mm      |

## ADDITIONAL PRODUCT DETAILS


Prior to installation, please read and understand all of the detailed instructions and safety notices provided in the nVent LENTON Cadweld Rebar Splicing System instruction manual.

Brushes must be kept free of grease, oil and other contaminants that could evolve gas and cause porosity in the filler material.

Do not reverse the cleaning brush while it is engaged with the reinforcing steel bar.

Eye protection should be used when using power-driven cleaning brushes.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE