We connect and protect

EuropacPRO 19" Subrack Kit for Backplane, Slide Rail, 3 U, 355 mm

Power Utilities

CATALOG NUMBER

24553-134





Non-shielded subrack for backplane, subrack can be assembeld on slide rails to support the subrack inside a cabinet.

CERTIFICATIONS

RoHS COMPLIANT

FEATURES

Subrack with side panel type F ("Flexible"), 19" bracket is depth-adjustable
Subrack can be used with slide rails
Rear horizontal rails for backplane mounting with insulation strip

Installed load up to 11 kg

Threaded insert, insulation strip pre-fitted

PRODUCT ATTRIBUTES

Product Type: Subrack/Chassis

Rack Height: 3 U

Rack Width: 84 HP

Depth: 355 mm

For Mounting: Backplane

Board Depth: 160 mm; 220 mm; 280 mm; 340 mm

EMC Shielding: No

Gasket Type: Stainless Steel

Static Load: 11 kgf

Handle Included: No

Mounting: Rack

Complies With: IEC 60297-3-103

Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

Alternative product for older EuropacLab and Europac subrack series.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.