

Front Panel, Anodized With Untreated Edges, Unshielded

Power Utilities



Front Panel, anodized with untreated edges, unshielded. The panels enable mounting on horizontal rails.

CERTIFICATIONS



FEATURES

Partial width front panel, Al, 2.5 mm

Al, clear anodized, untreated edges

SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Rack Width	Package Quantity	Handle Type	Mounting	Front Finish
30818-434	4 U	84 HP	1	None	Screw-on Front	Anodized
30818-598	6 U	84 HP	1	None	Screw-on Front	Anodized

CatalogNumber	Rack Height	Rack Width	Package Quantity	Handle Type	Mounting	Front Finish
30818-271	2 U	84 HP	1	None	Screw-on Front	Anodized
30818-310	3 U	42 HP	1	None	Screw-on Front	Anodized
30818-577	6 U	63 HP	1	None	Screw-on Front	Anodized
30818-331	3 U	63 HP	1	None	Screw-on Front	Anodized
30818-352	3 U	84 HP	1	None	Screw-on Front	Anodized
30818-556	6 U	42 HP	1	None	Screw-on Front	Anodized
30810-433	3 U	2 HP	5	None	Screw-on Front	Anodized
30818-747	6 U	2 HP	5	None	Screw-on Front	Anodized
30818-275	3 U	6 HP	5	None	Screw-on Front	Anodized
30818-272	3 U	3 HP	5	None	Screw-on Front	Anodized
30818-276	3 U	7 HP	5	None	Screw-on Front	Anodized
30818-277	3 U	8 HP	5	None	Screw-on Front	Anodized
30818-274	3 U	5 HP	5	None	Screw-on Front	Anodized
30818-279	3 U	10 HP	5	None	Screw-on Front	Anodized
30818-281	3 U	12 HP	5	None	Screw-on Front	Anodized
30818-282	3 U	14 HP	5	None	Screw-on Front	Anodized
30818-273	3 U	4 HP	5	None	Screw-on Front	Anodized
30818-289	3 U	21 HP	5	None	Screw-on Front	Anodized

CatalogNumber	Rack Height	Rack Width	Package Quantity	Handle Type	Mounting	Front Finish
30818-296	3 U	28 HP	5	None	Screw-on Front	Anodized
30818-518	6 U	4 HP	5	None	Screw-on Front	Anodized
30818-519	6 U	5 HP	5	None	Screw-on Front	Anodized
30818-535	6 U	21 HP	5	None	Screw-on Front	Anodized
30818-542	6 U	28 HP	5	None	Screw-on Front	Anodized
30818-530	6 U	16 HP	5	None	Screw-on Front	Anodized
30818-528	6 U	14 HP	5	None	Screw-on Front	Anodized
30818-526	6 U	12 HP	5	None	Screw-on Front	Anodized
30818-520	6 U	6 HP	5	None	Screw-on Front	Anodized
30818-524	6 U	10 HP	5	None	Screw-on Front	Anodized
30818-522	6 U	8 HP	5	None	Screw-on Front	Anodized
30818-521	6 U	7 HP	5	None	Screw-on Front	Anodized

Table 2/3

Catalog Number	Rear Finish	Treated Edges	Complies With	EMC Shielding	Height	Material
30818-434	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	172.9 mm	Aluminum
30818-598	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum
30818-271	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	84 mm	Aluminum

CatalogNumber	Rear Finish	Treated Edges	Complies With	EMC Shielding	Height	Material
30818-310	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum
30818-577	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum
30818-331	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum
30818-352	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum
30818-556	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum
30810-433	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum
30818-747	Anodized	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum
30818-275	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum
30818-272	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum
30818-276	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum
30818-277	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum
30818-274	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum
30818-279	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum
30818-281	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum
30818-282	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum

CatalogNumber	Rear Finish	Treated Edges	Complies With	EMC Shielding	Height	Material
30818-273	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum
30818-289	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum
30818-296	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum
30818-518	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum
30818-519	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum
30818-535	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum
30818-542	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum
30818-530	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum
30818-528	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum
30818-526	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum
30818-520	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum
30818-524	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum
30818-522	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum
30818-521	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum

Table 3/3

Catalog Number	Product Type	Type	Width
----------------	--------------	------	-------

30818-434	Front Panel	Front Panel without Handle	426.4 mm
30818-598	Front Panel	Front Panel without Handle	426.4 mm
30818-271	Front Panel	Front Panel without Handle	426.4 mm
30818-310	Front Panel	Front Panel without Handle	213 mm
30818-577	Front Panel	Front Panel without Handle	319.7 mm
30818-331	Front Panel	Front Panel without Handle	319.7 mm
30818-352	Front Panel	Front Panel without Handle	426.4 mm
30818-556	Front Panel	Front Panel without Handle	213 mm
30810-433	Front Panel	Front Panel without Handle	9.8 mm
30818-747	Front Panel	Front Panel without Handle	9.8 mm
30818-275	Front Panel	Front Panel without Handle	30.1 mm
30818-272	Front Panel	Front Panel without Handle	14.9 mm
30818-276	Front Panel	Front Panel without Handle	35.2 mm
30818-277	Front Panel	Front Panel without Handle	40.3 mm
30818-274	Front Panel	Front Panel without Handle	25 mm
30818-279	Front Panel	Front Panel without Handle	50.5 mm
30818-281	Front Panel	Front Panel without Handle	60.6 mm
30818-282	Front Panel	Front Panel without Handle	70.8 mm
30818-273	Front Panel	Front Panel without Handle	20 mm

30818-289	Front Panel	Front Panel without Handle	106.3 mm
30818-296	Front Panel	Front Panel without Handle	141.9 mm
30818-518	Front Panel	Front Panel without Handle	20 mm
30818-519	Front Panel	Front Panel without Handle	25 mm
30818-535	Front Panel	Front Panel without Handle	106.3 mm
30818-542	Front Panel	Front Panel without Handle	141.9 mm
30818-530	Front Panel	Front Panel without Handle	80.9 mm
30818-528	Front Panel	Front Panel without Handle	70.8 mm
30818-526	Front Panel	Front Panel without Handle	60.6 mm
30818-520	Front Panel	Front Panel without Handle	30.1 mm
30818-524	Front Panel	Front Panel without Handle	50.5 mm
30818-522	Front Panel	Front Panel without Handle	40.3 mm
30818-521	Front Panel	Front Panel without Handle	35.2 mm

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE